
3M™ Marine Reconditioning & Maintenance





3M[™] Marine Boat Reconditioning and Maintenance Products Featuring Unique 3M Marine Products and Protective Waxes







Fiberglass Boat Reconditioning (Gelcoat)

Surface Condition	Reconditioning Purpose	The One Step Solution
Clean, non-stained, non- oxidized boats	Protect surface	 3M[™] Marine Ultra Performance Paste Wax 3M[™] Marine Protective Liquid Wax
Smudge marks or water spots	In season cleaning and to extend protection	• 3M™ Marine Clean and Shine
Light to medium oxidation	Clean, Polish and protect surface	3M [™] Marine Fiberglass Cleaner and Wax
Heavy oxidation, chalking, fading, minor scratches, rust and exhaust stains	Restore, clean, polish and protect surface	• 3M [™] Marine Fiberglass Restorer and Wax

3M™ Marine Finishing Systems
Innovative solutions for every finishing application

	Heavy Oxidation Finishing System	Light to Medium Oxidation Finishing System	
Step			Step
0	3M™ Marine Fiberglass Restorer and Wax Best used with any Superbuff™ Compound Pad	3M [™] Marine Fiberglass Cleaner and Wax Best used with any Superbuff [™] Compound Pad	0
	For added protection or w	hen follow-up wax is needed	
2	3M™ Marine Ultra Performance Paste Wax Best used with any Superbuff™ Polishing Pad	3M™ Marine Ultra Performance Paste Wax Best used with any Superbuff™ Polishing Pad	2
	For regular touch-up ar	nd maintenance as needed	
3	3M™ Marine Clean and Shine Wax with soft cloth or 3M High Performance Wipe	3M™ Marine Clean and Shine Wax with soft cloth or 3M High Performance Wipe	3

Boat Reconditioning and Maintenance Products

3M™ Marine Fiberglass Restorer and Wax

Designed to remove HEAVY oxidation, chalking, fading, minor scratches,

rust and exhaust stains; plus provide protection on fiberglass/ gelcoat. Unique formulation combines a rubbing compound with a special blend of waxes which restore shine and protect in



one application. Available in liquid and paste versions.

Product Ref.	Contents	Quantity Per Case
09005	500ml (Liquid)	6
09006	1l (Liquid)	6
09007	3,78l (Liquid)	2
09012	510g (Paste)	6



3M™ Marine Fiberglass Cleaner and Wax




Designed to remove LIGHT to MEDIUM oxidation, clean, polish and protect fiberglass/gelcoat. Unique liquid formulation combines a compound with a special blend of waxes which restore shine and protect in one application.



Product Ref.	Contents	Quantity Per Case
09010	1I (Liquid)	6



3M[™] Marine Metal Restorer and Polish





Product Ref.	Contents	Quantity Per Case
09018	150g (Paste)	20
09019	500g (Paste)	6



3M™ Marine Protective Liquid Wax

Designed to provide high gloss and protect fiberglass/gelcoat, marine topside paints, painted aluminum and marine metal parts. A special formulation which uses reactive chemistry and actually bonds to the boats surface to provide a durable protective surface. Easy on/exceptionally easy off formula which also retards ultraviolet (U.V.) light damage.




Product Ref.	Contents	Quantity Per Case
09027	1I (Liquid)	6

Boat Reconditioning and Maintenance Products

3M™ Marine Ultra Performance Paste Wax

Contains the unique 3M polymer technology which provides the durability of an acrylic, with the soil release and water beading properties of a fluoropolymer and silicone. This innovative new product will leave a protective high gloss finish on marine fiberglass gelcoat,



Product Ref.	Size	Quantity Per Case
09030	269a	6

3M™ Marine Clean and Shine

3M Marine Clean and Shine is a quick and easy, "spray on/wipe off" product that recaptures that "just waxed" look and feel. Excellent for use on wet or dry surfaces; no water needed! May also be used to enhance the shine of your boats fiberglass gelcoat, marine topside paint, painted aluminum or metal parts. Simply spray on sections that are still wet after washing and rinsing, and revitalize the finish by wiping the surface dry.

Product Ref.	Size	Quantity Per Case
09033	444ml	6

3M™ Marine Superbuff™ Pad

A 150mm diameter buffing pad with a wool pile on both sides of the pad. The 3M Marine Superbuff Pad allows the do-it-your-selfer to recondition and maintain their boat, using their drill to obtain a high-gloss finish like the professional who uses high-speed tools. The unique double face construction allows both sides of the pad to be used. It



has a lightweight support pad built into each pad, thus eliminating the need for heavy rubber back-up pads. Designed to fit any standard electric drill with its arbor and hex-head nut.

Product Ref.	Buffs Per Case
09038	12

3M™ Marine Outdoor Vinyl Cleaner

Designed to clean, condition and protect marine vinyl and rubber components. Unique gel formula provides durable protection in exterior, as well as interior applications. Gel formula gives you better application control than liquids. A little bit goes a long way. Very good performances on inflatable boats.



Product Ref.	Contents	Quantity Per Case
09023	236ml (Gel)	6

3M™ Marine Vinyl Cleaner and Restorer

Cleans, shines, conditions and protects vinyl, rubber and plastic surfaces. Deep cleans dirt and grime, enhances appearance. Restores natural sheen, protects surfaces. Fresh lemon scent.



Product Ref.	Contents	Quantity Per Case
09029	444ml	6

3M™ Marine Clear Plastic Restorer

Safely cleans and removes fine scratches and haziness from most marine plastics. Can be used on most tinted plastics: test for suitability. For best results on polycarbonate plastic (*Lexan®, Tuffak®, etc) use by machine.



Product Ref.	Contents	Quantity Per Case
09044	250ml	6

*Lexan® is a registered Trademark of General Electric Co., and Tuffak® is a registered trademark of Atohaas Americas Inc.

3M™ Acryl-Marine Putty — White

Designed specifically for the boat repair market, this putty is recommended for filling pinholes, scratches and other surface defects on hulls. Its white color minimizes



the possibility of color showing through the final coat as can happen when using colored putties beneath white paint. Other advantages include easy sanding, fast drying, spreads easily, and has low shrinkage.

Product Ref.	Container Size	Quantity Per Case
05662	200g	24



3M[™] **Marine** Boat Reconditioning and Maintenance Products

Surface Condition	Reconditioning Purpose	The One Step Solution
Plastic with fine scratches and haziness	Removes scratches and restores clarity	3M™ Marine Clear Plastic Restorer
Dull & dirty vinyl	Rejuvenate & restore luster	 3M™ Marine Vinyl Cleaner and Restorer 3M™ Marine Outdoor Vinyl Cleaner, Conditioner and Protector
Dull, oxidized, aluminum, stainless steel, brass, bronze & other marine metals	Clean, polish & restore luster	• 3M™ Marine Metal Restorer & Polish



Marine Trades
3M United Kingdom PLC

28 Great Manchester Street Manchester M15 4PA Tel: +44 (0)161 237 6130 Fax: +44 (0)161 237 3371

Email: transportation_solutions.uk@mmm.com or visit our website at www.3m.com/uk