

3M Graphics Market Center  
Sign Fabrication Products



# Improving Your Efficiencies



# Table of Contents

## Surface Preparation

3M™ Imperial™ Roloc™ Discs .....	4
3M™ Imperial™ Fibre Discs .....	4
3M™ Stikit™ Gold Disc Rolls .....	4
3M™ Overspray Protective Sheeting .....	4
Scotch® Steel Gray Masking Paper .....	4
Scotch® Performance Masking Tape 233+ .....	4
3M™ Overspray Masking Liquid Dry .....	5
3M™ Prep Scuff .....	5
3M™ Prep Solvent-70 .....	5

## Painting

### 3M™ PPS™ Paint Preparation System

Mini Cup Kits .....	5
Lids and Liners .....	5
Mixing Cups and Collars .....	6
Type H/O Pressure Cup .....	6
Mylar Film Inserts .....	6
Adapters .....	7–10
Spray Gun Holders .....	11
System Carrier .....	11
Cartridge Strainer .....	11
Lid Dispenser .....	11
Large Liner Dispenser .....	11
3M™ Detailing Squeeze Bottle .....	11
3M™ Paint Buster™ Hand Cleaner .....	11

## Painting (cont.)

### 3M™ PPS™ SUN GUN™ Color Matching Light

Color Matching Light Kit .....	12
Color Corrective Bulb .....	12
NiCad Battery Pack .....	12
Battery Charger with Power Supply Chord .....	12

## Surface Finishing — Compounding

3M™ Super Duty Rubbing Compound .....	13
3M™ Perfect-It™ 3000 Extra Cut Rubbing Compound .....	13
3M™ Perfect-It™ 3000 Swirl Mark Remover .....	13
3M™ Perfect-It™ 3000 Trizact™ Spot Finishing Material .....	13
3M™ Perfect-It™ III Compounding Pad — 9" .....	13
3M™ Perfect-It™ Foam Compounding Pad — 8" .....	13
3M™ Perfect-It™ Plus Foam Compounding Pad — 8" .....	14
3M™ Hookit™ SBS™ Backup Pad .....	14
3M™ Perfect-It™ Foam Polishing Pad — 8" .....	14
3M™ Perfect-It™ Plus Foam Polishing Pad — 8" .....	14

## Surface Finishing — Detailing

3M™ Performance Finish .....	14
3M™ All Purpose Cleaner & Degreaser .....	14

# Table of Contents

## Welding/Bonding/Sealing

3M™ Welding and Spark Deflection Paper .....	15
3M™ Weldable Primer .....	15
3M™ High Performance Welding Drape .....	15
3M™ Trim Adhesives .....	15
MixPac® Applicator Gun .....	16
3M™ Automix™ Mixing Nozzle .....	16
3M™ Piranha™ Advanced Finishing Putty .....	16
Duramix™ Repair Products .....	16
3M™ Lightweight Body Filler .....	16
3M™ Flexiclear™ Body Seam Sealer .....	17
3M™ Super Silicone Sealant.....	17
3M™ Spreaders.....	17
3M™ Creme Hardener .....	17
3M™ General Purpose Adhesive Cleaner .....	17
3M™ Woodgrain and Stripe Remover .....	17
3M™ Woodgrain and Stripe Adhesive Remover.....	17

## Safety

3M™ Respirators.....	18–19
3M™ Organic Vapor Monitor .....	19
3M™ GVP PAPR Kit.....	20
3M™ Hearing Protection.....	21
3M™ Eye Protection .....	21
3M™ Health and Services (Training Programs) .....	22

## Additional Information

Part Number Index.....	23
3M Warranty.....	23

# Surface Preparation



## 3M™ Imperial™ Roloc™ Discs

- Molded plastic backing improves grinding efficiency.
- Self-sharpening, cooler running, and longer lasting.
- Use for weld grinding, paint removal and metal grinding.

Part Number	Grade	Discs Per Box	Boxes Per Case
<b>3" Diameter</b>			
051131-01343	24	15	6
051131-01344	36	15	6
051131-01345	50	15	6
051131-01346	80	15	6
<b>Disc Pad Assembly</b>			
051131-05540	3" x 1/4" shank	1	10



## 3M™ Stikit™ Gold Disc Rolls

- Designed for use on paint and primer.
- Durable and long lasting abrasive products.
- Pressure-sensitive adhesive (PSA) backing.

Part Number	Grade	Discs Per Roll	Rolls Per Case
<b>6" Diameter</b>			
051131-01432	P500	175	6
051131-01434	P400	175	6
051131-01433	P360	175	6
051144-01435	P320	175	6
051144-01436	P280	175	6
051144-01437	P240	175	6
051144-01438	P220	175	6
051144-01439	P180	175	6
051144-01440	P150	175	6
051144-01441	P120	125	10
051144-01442	P100	125	10
051144-01443	P80	125	10



## 3M™ Imperial™ Fibre Discs

- 3M's performance class abrasive.
- Improved construction resists loading while generating less heat.
- Use for metal grinding and paint stripping.

Part Number	Grade	Discs Per Bag	Bags Per Case
<b>5" Diameter</b>			
051131-01945	24	10	5
051131-01944	36	10	5
051131-01943	50	10	5

## 3M™ Overspray Protective Sheeting (Now Paintable)

- Uniquely formulated to provide excellent paint adherence.
- High-density, tear-resistant, clear film.
- Durable film that is treated for excellent paint overspray adhesion.
- Twelve foot film folded to three feet for easy one-person application.
- Sixteen foot width accommodates larger vehicles (i.e. mini-vans, sport utilities, pick-up trucks, etc.) for more effective overspray protection.
- Use with Masker PN06780.



Part Number	Size	Rolls Per Case
051131-06727	12' x 400'	1
051131-06728	16' x 350'	1
<b>Bulk</b>		
051131-06742	20' x 250'	1

## Scotch® Steel Gray Masking Paper

- Strong, flexible and pliable.
- Formulated to resist penetrations of solvents, lacquers or enamels.
- Variety of sizes: 12" to 18" widths for general masking— 3" or 6" widths for headlights, taillights, door jambs and bumpers.



Part Number	Size	Rolls Per Case
021200-06503	3" x 1000'	6
021200-06506	6" x 1000'	6
021200-06509	9" x 1000'	4
021200-06512	12" x 1000'	3
021200-06518	18" x 1000'	2
021200-06524	24" x 1000'	1
021200-06536	36" x 1000'	1

## Scotch® Performance Masking Tape 233+

- High performance masking tape designed to exceed the needs of today's collision repair shops.
- Highly conformable and has a specially formulated adhesive system which offers improved adhesive transfer resistance on rubber moldings and painted surfaces.
- Performs consistently under a variety of climactic conditions.
- Provides outstanding paint lines and a controlled, consistent unwind.



Part Number	Size	Rolls Per Case
<b>Bulk</b>		
051131-26330	6mm x 55m (1/4" applications)	96
051131-26332	12mm x 55m (1/2" applications)	48
051131-26334	18mm x 55m (3/4" applications)	48
051131-26336	24mm x 55m (1" applications)	24
051131-26338	36mm x 55m (1-1/2" applications)	16
051131-26340	48mm x 55m (2" applications)	12
051131-26341	72mm x 55m (3" applications)	8

## Surface Preparation

### 3M™ Overspray Masking Liquid Dry

- Water-based masking liquid.
- Dries to a non-tacky film.
- Protects against paint and primer overspray.
- Traps dust and dirt under its protective film.
- Safe to use on all thoroughly cured paint surfaces.



Part Number	Container Size	Containers Per Case
051131-06847	1 Gallon	4
051131-06851	5 Gallon	1
051131-06856	15 Gallon	1
051131-06857	55 Gallon	1

### 3M™ Prep Solvent-70

- A water-based solvent used to remove oil, wax, grease and silicone from surfaces prior to coating.
- Effectively cleans metal, primed metal and painted surfaces prior to the application of primer or paint.
- Rated at 70 grams per liter of volatile organic compounds (VOC).
- Currently meets regulations governing VOC emissions of surface preparation solvents.



Part Number	Container Size	Containers Per Case
051135-08983	1 Gallon	4

### 3M™ Clear Blend Prep Scuff

- Excellent for sail panel blends.
- Perfect for gold/silver/pearl metallic.
- Prep clear coat areas and critical blends.
- Easy "buff back."
- Provides optimum clear prep adhesion.



Part Number	Size	Color	Rolls Per Case
051131-07745	4-3/4" x 15'	Gold	3

### 3M™ Primer Prep Scuff

- Prep E-coated panels quickly.
- Scuffs faster without leveling.
- Use on door jambs and underneath hoods.
- Provides optimum primer prep adhesion.



Part Number	Size	Color	Rolls Per Case
051131-07747	4-3/4" x 15'	Maroon	3

### 3M™ Color Prep Scuff

- Ideal for use on all panels.
- Scuffs faster and finer.
- Use for prep of color-coat areas and easy blends.
- Provides for optimum color prep adhesion.



Part Number	Size	Color	Rolls Per Case
051131-07748	4-3/4" x 15'	Gray	3

## Painting

### 3M™ PPS™ Paint Preparation System Mini Cup Kit

Kit includes:

- Two (2) cups and collars
- Fifty (50) lids and liners
- Twenty (20) plugs
- Two (2) inserts
- One (1) dispenser



Part Number	Description	Kits Per Case
051131-16113	Mini Cup Intro Kit	1

### 3M™ PPS™ Paint Preparation System Lids and Liners

- Contains lids, filters, liners and sealing caps.



Part Number	Size	Items Per Box	Boxes Per Case
051131-16000	Standard	50	1
051131-16114	Mini	50	1
051131-16024	Large	25	1

## Painting

### 3M™ PPS™ Paint Preparation System Mixing Cups and Collars

- Cups that incorporate collars.



Part Number	Size	Cups Per Box	Boxes Per Case
051131- <b>16001</b>	Standard	2	4
051131- <b>16115</b>	Mini	2	4
051131- <b>16023</b>	Large	1	4

### 3M™ PPS™ Paint Preparation System Type H/O Pressure Cup

- For use on pressure fed guns and turbine units.
- For use with PNs 16024 and 16000.



Part Number	Items Per Box	Boxes Per Case
051131- <b>16124</b>	1	2

### 3M™ PPS™ Paint Preparation System Mylar Film Inserts

- Mix ratio printed on clear film insert.
- Variety of sizes available for use with mini, regular or large cups.
- Paint company specific for your convenience.
- Film inserts must be placed between the hard cup and flexible liner.






Part Number	Size	Paint Company Specific Inserts	Inserts Per Box	Boxes Per Case
051131- <b>16055</b>	Regular	PPG1	100	1
051131- <b>16056</b>	Regular	PPG2	100	1
051131- <b>16057</b>	Regular	BASF1	100	1
051131- <b>16058</b>	Regular	BASF2	100	1
051131- <b>16059</b>	Regular	BASF3	100	1
051131- <b>16060</b>	Regular	DuPont	100	1
051131- <b>16061</b>	Regular	SW1	100	1
051131- <b>16062</b>	Regular	SW2	100	1
051131- <b>16064</b>	Regular	Sikkens	100	1
051131- <b>16065</b>	Regular	Generic	100	1
051131- <b>16066</b>	Mini	Generic	50	1
051131- <b>16072</b>	Regular	Standox & Spies-Hecker	100	1
051131- <b>16073</b>	Regular	Standox & Spies-Hecker	100	1
051131- <b>16074</b>	Large	Standox & Spies-Hecker	100	1
051131- <b>16075</b>	Large	Standox & Spies-Hecker	100	1
051131- <b>16076</b>	Regular	BASF	100	1
051131- <b>16077</b>	Large	BASF	100	1
051131- <b>16081</b>	Large	PPG1	100	1
051131- <b>16082</b>	Large	PPG2	100	1
051131- <b>16083</b>	Large	BASF1	100	1
051131- <b>16084</b>	Large	BASF2	100	1
051131- <b>16085</b>	Large	BASF3	100	1
051131- <b>16086</b>	Large	DuPont	100	1
051131- <b>16087</b>	Large	SW1	100	1
051131- <b>16088</b>	Large	SW2	100	1
051131- <b>16090</b>	Large	Sikkens	100	1
051131- <b>16091</b>	Large	Generic	100	1
051131- <b>16092</b>	Regular	AKZONOBEL GRIPGARD	100	1
051131- <b>16093</b>	Regular	AKZONOBEL GRIPGARD	100	1
051131- <b>16094</b>	Large	AKZONOBEL GRIPGARD	100	1
051131- <b>16095</b>	Large	AKZONOBEL GRIPGARD	100	1

**Note:** 3M™ PPS™ Paint Preparation System part numbered items are available through authorized distributors. Please inquire with your distributor, contact your local 3M Sales Representative or contact 3M for availability.

# Painting








## 3M™ PPS™ Paint Preparation System Adapters (Packaged 4 Adapters per Box)

Part Number	3M™ PPS™ Adapter Number/Size	3M Spray Gun Type	Make & Model of Paint Gun
<b>051131-16003</b> 	#2 16mm Female 1.5mm Thread		ADIR
			Advantage #90115
		A, H	AES-150
		H	AirVerter GG-100 HVLP
		A, H	Astro, Astro M-Star
		A, H	ATD
		H	CA Technologies, Jaguar
		H	Campbell DH-7900 HVLP (Menards)
		H	Cent Neu HVLP
			Goni 321
		H	Husky HDS-790 HVLP (Home Depot)
		A, H	Ingersoll Rand 210 Gravity Feed
		H	Iwata LPA-94
		A	Iwata VXL-949 Primer Gun
		A	Iwata W-400
		A	Iwata WR-400, LPH-400
		H	M-Star
		H	Mac-Econocoat
		H	Matco
			MSB
			NESCO 840, 870
			Nikota HVLP-G
		A, H	Porter-Cable PSH-1, PSH-3
		A	Sata Jet-B
		H	Sata NR-92, NR-95
		H	Sharpe FX-200 Non-HVLP
		H	Sharpe FX-300 HVLP
			Spray-It 522
			Star-III
			Sunex, 9002A
	Trem Pro		
	Vaper 1.4mm Base/Clear Gun		
	Vaper 1.7mm Primer Gun		
H	Warwick, 861-C, 863, 881-C		
<b>051131-16005</b> 	#4 12mm Female 1.0mm Thread	A	DeVilbiss Finishline (FLG-1), NTL-1261
<b>051131-16006</b> 	#5 12mm Male 1.5mm Thread		Defynik
		H	Sagola 403-G
		H	Sagola 4100-G, 4200-G
		H	Sagola 433-G
		H	Sagola 434-G
		H	Sagola 444-G
		H	Sagola 450-G
		A	Sata KL-Primer
			Sata MC-B-93 (Used with adapter taken off metal cup)

**Note:** 3M™ PPS™ Paint Preparation System part numbered items are available through authorized distributors. Please inquire with your distributor, contact your local 3M Sales Representative or contact 3M for availability.

## Painting

### 3M™ PPS™ Paint Preparation System Adapters (Packaged 4 Adapters per Box)









Part Number	3M™ PPS™ Adapter Number/Size	3M Spray Gun Type	Make & Model of Paint Gun
051131-16007 	#6 1/4 Male 19 Thread (BSP)	H	Aerometal, Super Fura 34
		H	Aerometal, Victoria 92, 2015
		H	AirGunsa, AZ-3
			Asturo Gravity
		H	Eminent E13
		H	Iwata LPH-300
		A	Iwata W-300
		H	Kremlin M21-G, Hti-G
051131-16008 	#7 3/8 Female 18 Thread (BSP)	H	AccuSpray, Issac
		H	Optima Gravity Feed Models: 500, 500i, 800, 800C, 800L, 800i
		H	TransStar-2
051131-16015 	#8 12mm Male 1.0mm Thread	H	GEO F/X (Walcom)
		H	Walcom GEO F/X
051131-16016 	#9 16mm Male 1.5mm Thread	H	AccuSpray, 05-100
		A	Sata Jet-90
		H	Sata KLC-B
		C	Sata KLC-RP
		H	Sata LM-2000
		H	Sata LM-92
		H	Sata MC-B Primer Gun
		H	Sata MC-B-90
		H	Sata NR-2000
			Sata QCC-Quick Cup Connector with Sata 96-719 QCC Adapter
		C	Sata RP-2000
		H	Warwick 827-C, 878
051131-16017 	#10 Elbow Swivel Nut 1/4 Female 19 Thread (BSP)	H	Apollo A-8200, Side Cup Mount
			DeVilbiss FUN, Gravity
		A	DeVilbiss JGX-501, 502
		H	DeVilbiss Touch-up Gun TGHV-635
		A	Graco 600 Side Cup Mount
		H	Iwata LPH-100, W-100G
		H	Iwata LPH-50 Mini Spray Gun
		A	Iwata RG3L Mini Air Brush
			Iwata W-71
			Meiji FSA Mini-Gun
		051131-16018 	#11 3/8 Male 18 Thread (NPS)
H	Sharpe Platinum HVLP		
A	Sharpe SGF-98		
H	Sharpe Titanium T-1 HVLP		
H	Snap-On (Sharpe Cobalt)		
051131-16022 	#12 10mm Male 1.0mm Thread	H	Sagola 475 Mini-Gun
		H	Sata Mini-Jet, Mini-Jet 4

**Note:** 3M™ PPS™ Paint Preparation System part numbered items are available through authorized distributors. Please inquire with your distributor, contact your local 3M Sales Representative or contact 3M for availability.



# Painting







## 3M™ PPS™ Paint Preparation System Adapters (Packaged 4 Adapters per Box)

Part Number	3M™ PPS™ Adapter Number/Size	3M Spray Gun Type	Make & Model of Paint Gun
051131-16053 	#14 7/16 Male 14 Thread	H	Binks Cub SLG, Mini-Gun
		H	DeVilbiss Sri, Mini-Gun
051131-16046 	#15 3/8 Male 19 Thread (BSP)	H	Binks 1.8 MGI-Primer
		H	Binks 630 HVLP, 95-G
		H	Binks BBR-HVLP
		H	Binks M1 -G
		A	DeVilbiss Finishline-2
		H	DeVilbiss Finishline-3
		A	DeVilbiss GFG-5
		A	DeVilbiss GFG-516, 517, GFG-618
		C	DeVilbiss GFG-670 PLUS
		H	DeVilbiss GFHV-510
		H	DeVilbiss Gti Millennium, 620-G
		H	Ecco 652-S
		H	Graco Delta HVLP-GF
051131-16102 	#16 3/8 Female 19 Thread (BSP)		Optima, All Gravity Feed Guns
			400, 500, 600, 700 and 800 Series
			All Siphon Feed Guns, Europe
051131-16111 	#17 1/4 Female 19 Thread (BSP)		Mini Siphon Guns, Europe
051131-16054 	#18 3/8 Female 18 Thread (NPS)	H	DeVilbiss TGHV 530 Siphon Feed
		A,H,C	Siphon Feed, Full Size USA
051131-16103 	#19 3/8 Female 19 Thread (BSP)	A	Iwata W-200 Siphon
		A,H,C	Siphon Feed, Full Size Europe
051131-16104 	#20 1/8 Male 27 Thread (UPSM)	H	Sharpe MFG, MPF Mini-Gun HVLP
051131-16105 	#21 14mm Female 1.0mm Thread	H	AccuSpray Mini-Gun
		H	AirVerter CT-100 Mini Spray Gun
		H	Astro Star GF6S Mini-Gun HVLP
		A, H	ATD-6845 Mini-Gun
		H	Central Pneumatic Mini-Gun HVLP
		H	Cornwell PSG-1200 Mini-Gun
			Ingersoll Rand 200G
		H	Mac Mini-Gun HVLP
			Matco RL-75 Mini-Gun
		H	Mountain Star Mini
			NESCO 808 Mini
		A, H	Porter-Cable PSH2 Mini-Gun
		H	Sharpe FX-100 Mini HVLP
		H	Snap-On BF-325 Mini HVLP
		H	Vaper 1.0mm Mini-Jet Gun
H	Warwick 828-C, Mini HVLP		

**Note:** 3M™ PPS™ Paint Preparation System part numbered items are available through authorized distributors. Please inquire with your distributor, contact your local 3M Sales Representative or contact 3M for availability.

## Painting

### 3M™ PPS™ Paint Preparation System Adapters (Packaged 4 Adapters per Box)

Part Number	3M™ PPS™ Adapter Number/Size	3M Spray Gun Type	Make & Model of Paint Gun
051131-16106 	#22 8mm Male .75mm Thread		Walcom Touch-up Gun STM HVLP
051131-16109 	#23 1/4 Female 1/8 Thread (NPS)		Balkamp (NAPA)
			Binks 115 Mini Siphon Feed
			Campbell Mini Siphon Feed
			Craftsman 9-15002
		A	DeVilbiss EGA-503 Mini Siphon Feed
		H	DeVilbiss Touch-up Gun EGHV-531
		A	Sharpe 555 Mini Siphon Gun
		H	Snap-On BF-400 Mini HVLP
		Snap-On BF-510 Detail	
051131-16110 	#24 Elbow Swivel Nut 1/4 Female 18 Thread (NSP)	H	Snap-On BF-515 Mini HVLP, Side Cup Mount
051131-16116 	#25 1/4 Female 19 Thread (BSP)	H	DeVilbiss FUN, Siphon
		A	Iwata W-100, Siphon
			Kinky Creamy 88, Siphon (may be used as Siphon Feed Cup Mount)
051131-16118 	#26 11mm Male 1.0mm Thread	H	DeVilbiss Finishline-4 HVLP Mini Gravity Feed Spray Gun
051131-16119 	#27 16mm Male 1.5mm Thread	H	DeVilbiss Finishline-4 HVLP Gravity Feed Spray Gun

If you do not find the proper adapter for your spray gun, please contact your authorized distributor, your local 3M Sales Representative or 3M for availability.



**Note:** 3M™ PPS™ Paint Preparation System part numbered items are available through authorized distributors. Please inquire with your distributor, contact your local 3M Sales Representative or contact 3M for availability.


# Painting



### 3M™ PPS™ Spray Gun Holders

- Convenient spray gun storage.
- Four sizes available.

Part Number	Description	Quantity Per Case
051131-16236	Single, Holds 1 spray gun Magnetic	5
051131-16237	Double, Holds 2 spray guns Bench Mount	1
051131-16238	Quad, Holds 4 spray guns Wall Mount	1



### 3M™ PPS™ Paint Preparation System Carrier

- Six-pack Paint Preparation System cup holder with wall attachment hardware (PN16010).
- Four-pack Paint Preparation System mini-cup holder (PN16617). Can be used by itself or it can be attached to the side of PN16010.

Part Number	Size/Description	Quantity Per Case
051131-16010	Regular Cup Carrier	1
051131-16117	Mini Cup Carrier	1

### 3M™ PPS™ 200 Micron Cartridge Strainer

- Provides efficient and consistent straining of paint materials.
- Enables gun to spray cleaner with less waste and mess.



Part Number	Size	Strainers Per Pack	Packs Per Case
051131-16013	200 Micron	20	10

### 3M™ PPS™ Paint Preparation System Lid Dispenser

- Lid dispenser.



Part Number	Quantity Per Case
051131-16099	1

### 3M™ PPS™ Paint Preparation System Large Liner Dispenser

- Large liner dispenser.



Part Number	Quantity Per Case
051131-16019	1

### 3M™ Detailing Squeeze Bottle

- Wash bottle for cleaning Paint Preparation System.



Part Number	Quantity Per Case
051131-37720	24

### 3M™ Paint Buster™ Hand Cleaner

- A cream-type hand cleaner.
- Offers superior performance in the removal of lacquer, enamel and urethane paints, primers, putties, plastic fillers, adhesives and automotive sealants from skin.



Part Number	Size	Tubes Per Case
051131-05975	10.5 fl. oz. Tube	12

**Note:** 3M™ PPS™ Paint Preparation System part numbered items are available through authorized distributors. Please inquire with your distributor, contact your local 3M Sales Representative or contact 3M for availability.

# Painting

## 3M™ PPS™ SUN GUN™ Color Matching Light Kit

- Helps achieve near perfect color match.
- Improve cycle times, C.S.I. ratings, customer relations and reputation for quality.
- Minimize metamerism and identify pin holes, sand scratches and swirl marks before applying primer or basecoat.
- Reduces the chance of costly re-work or comebacks.
- Kit (PN16400) contains:
  - One (1) 3M™ PPS™ SUN GUN™ Color Matching Light
  - One (1) 3M™ PPS™ SUN GUN™ Color Correcting Bulb PN16399
  - One (1) 3M™ PPS™ SUN GUN™ NiCad Battery Pack PN16398
  - One (1) 3M™ PPS™ SUN GUN™ Battery Charger w/Power Supply and Cord PN16396
  - One (1) Durable Protective Carrying Case
  - One (1) Safety and Instruction Manual
  - One (1) Warranty Registration Card



## 3M™ PPS™ SUN GUN™ Color Corrective Bulb

- 35 watts.
- For use only in the 3M™ PPS™ SUN GUN™ Color-Matching Light.



Part Number	Description	Bulbs Per Case
051131-16399	35 Watt Bulb	6

Part Number	Description	Kits Per Case
051131-16400	Kit	1

## 3M™ PPS™ SUN GUN™ NiCad Battery Pack

- For use only in the 3M™ PPS™ SUN GUN™ Color-Matching Light.



Part Number	Description	Quantity Per Case
051131-16398	Battery Pack	4



16400



## 3M™ PPS™ SUN GUN™ Battery Charger with Power Supply and Chord

- For use only in the 3M™ PPS™ SUN GUN™ NiCad (Nickel-Cadmium) Battery Pack.

Part Number	Description	Quantity Per Case
051131-16396	Battery Charger	1

**Note:** 3M™ PPS™ Paint Preparation System part numbered items are available through authorized distributors. Please inquire with your distributor, contact your local 3M Sales Representative or contact 3M for availability.

## Surface Finishing – Compounding

### 3M™ Super Duty Rubbing Compound

- Aggressive compound.
- Remains wet on the job with little or no mess.
- Maintains high rate of cut with constant pressure.
- Buffs to high gloss with minimum of swirl marks.
- Excellent for hand or machine use.
- VOC content less than 17%.



Part Number	Container Size	Containers Per Case
051131-05954	1 Quart	12

### 3M™ Perfect-It™ 3000 Swirl Mark Remover

- Quickly and effectively removes compound swirl marks.
- Produces outstanding finish — great for black cars.
- Good handling characteristics.
- Easy cleanup.



Part Number	Container Size	Containers Per Case
051131-06064	1 Quart	6

### 3M™ Perfect-It™ 3000 Extra Cut Rubbing Compound

- Excellent cutting compound combined with a fine finish.
- Removes grade P1200 and finer sand scratches without filling.
- Easy to detail from door jambs, cracks and moldings.
- Excellent handling characteristics.
- Recommended for hard paints.
- VOC content less than 17%.
- Replaces PN05936 (Quart) effective April 1, 2005.



Part Number	Container Size	Containers Per Case
051131-06060	1 Quart	6



### 3M™ Perfect-It™ 3000 Trizact™ Spot Finishing Material

- Quickly and effectively removes compound swirl marks.
- Produces outstanding finish — great for black cars.
- Good handling characteristics.
- Easy cleanup.

Part Number	Container Size	Containers Per Case
051131-06070	1 Quart	6

### 3M™ Perfect-It™ III Compounding Pad — 9"

- Single-sided.
- 100% wool pad.
- Untwisted yarn.
- Excellent for hard paints.
- Aggressive fine cutting pad.



Part Number	Description	Pads Per Bag	Bags Per Case
051131-05719	9" Wool Compounding Pad	1	24



### 3M™ Perfect-It™ Foam Compounding Pad — 8"

- Utilizes a 3M patented convoluted foam face.
- Easily attaches to 3M™ Backup Pads (PN05717).
- Fits all standard (5/8" shaft) slow-speed polishers.

Part Number	Description	Pads Per Bag	Bags Per Case
051131-05723	8" Convoluted Foam Compounding Pad	2	12

## Surface Finishing – Compounding

### 3M™ Perfect-It™ Plus Foam Compounding Pad — 8"

- Utilizing 3M's patented convoluted foam face.
- New reduced diameter loop attachment backing for added edge protection.
- Attaches to either 3M™ Hookit™ Backup Pad (PN05717).
- Fits all standard 5/8 inch shaft slow-speed polishers.



### 3M™ Hookit™ SBS™ Backup Pad

- Designed to be used with 3M™ Compounding Pads (PNs 05711, 05719, and all foam pads).
- Designed to be used with 3M™ Polishing Pads (PNs 05713 and all foam pads).

#### Part Number

051131-**05717**

#### Pads Per Case

1

Part Number	Description	Pads Per Bag	Bags Per Case
051131- <b>05737</b>	8" Convoluted Foam Compounding Pad	1	6

### 3M™ Perfect-It™ Foam Polishing Pad — 8"

- Convoluted foam face produces wheel/swirl free paint finish when used with 3M™ Perfect-It™ Foam Polishing Pad Glazes.
- Attaches to 3M™ Hookit™ Back Up Pad (PN 05717).



### 3M™ Perfect-It™ Plus Foam Polishing Pad — 8"

- Utilizes a 3M patented convoluted foam face.
- New reduced diameter loop attachment backing for added edge protection.
- Attaches to either 3M™ Hookit™ Backup Pad (PN05717).
- Fits all standard (5/8" shaft) slow-speed polishers.

#### Part Number

051131-**05738**

#### Description

8" Convoluted Foam Polishing Pad

#### Pads Per Bag

1

#### Bags Per Case

6

Part Number	Pads Per Bag	Bags Per Case
051131- <b>05725</b>	2	12

## Surface Finishing – Detailing

### 3M™ Performance Finish

- Long lasting.
- Easy on, easy off application.
- Extreme shine.
- Alternative to wax.



Part Number	Container Size	Containers Per Case
051131- <b>38112</b>	1 Quart	6
051131- <b>39030</b>	1 Pint	6



### 3M™ All Purpose Cleaner & Degreaser — Concentrate

- Cleaner/degreaser concentrate for exterior and interior cleaning.
- Use for vinyl, cloth or carpet cleaning.
- Contains no silicones; designed for paint shop environment.
- Dilution — 1 part product to 15 parts water (makes 16 gallons) for degreasing, doorjams and pre-spotting carpets.
- Dilution — 1 part product to 30 parts water (makes 31 gallons) for general purpose interior cleaning.

#### Part Number

051131-**38350**

#### Container Size

1 Gallon

#### Containers Per Case

4

## Welding/Bonding/Sealing

### 3M™ Welding and Spark Deflection Paper

- Flame retardant.
- Repositionable adhesive on one side.
- Formulated to protect vertical surfaces, glass and paint from welding spatter and grinding sparks.
- Easy to use roll form.



Part Number	Roll Size	Rolls Per Case
051131-05916	24" x 150'	2

### 3M™ Weldable Primer

- An aerosol coating designed to be applied to metal surfaces prior to welding which provides corrosion protection after the weld.
- Dries fast (5-10 minutes).
- Minimizes MIG weld spatter.
- Meets MIR requirements



Part Number	Can Size	Cans Per Case
051131-05917	12.75 oz. Aerosol	6



### 3M™ High Performance Welding Drape

- Extreme resistance to heat, sparks, welding spatter and flames.
- Ideal for protection from automotive welding spatter and grinding sparks.
- Very lightweight, conformable and easy to handle.
- Excellent wear and tear resistance.
- Easy to clean by brushing or shaking.

Part Number	Size	Quantity Per Case
051131-05919	57" x 80"	1

### 3M™ Spray Trim Adhesive Clear

- An adhesive for attaching lightweight trim materials (upholstery cloth, trunk liners) to metal and other surfaces.
- Ideal for position-bonding applications where mechanical fasteners will be used.
- May be used to bond styrofoam.



Part Number	Can Size	Cans Per Case
051131-08074	24 fl. oz. Aerosol	6

### 3M™ General Trim Adhesive Clear

- A low VOC, high-strength adhesive for bonding automotive materials (carpeting, jute pads, fabrics, plastics) to metal and other surfaces.
- Good heat and water resistance.
- Not recommended for bonding polystyrene foam. (For bonding polystyrene foam, use 3M™ Spray Trim Adhesive PN08074).



Part Number	Net Wt.	Cans Per Case
051135-08088	16.25 oz. Aerosol	6

### 3M™ Super Trim Adhesive

- A contact adhesive designed for bonding vinyl tops, heavyweight headliners and hood silencer pads where high strength and heat resistance are needed.



Part Number	Net Wt.	Cans Per Case
051135-08090	18 oz. Aerosol	6

## Welding/Bonding/Sealing



### MixPac® Applicator Gun

- For use with Duramix™ Plastic Repair products (PNs 04240 and 04247).
- Easy-to-use dispensing gun.
- Can dispense 2-1 or 1-1 MixPac® cartridges without plunger replacement.
- Easily dispenses urethanes and epoxies in 200ml cartridges.
- Heavy-duty metal construction.
- To order PN08117, call Shopware at 1-800-877-9344.

Part Number	Description	Quantity Per Case
051135-08117	Manual Applicator Gun	1

MixPac® is a registered trademark of MixPac® Systems AG, Switzerland.



### Duramix™ Semi-Rigid Plastic Repair

- A material for repairing virtually all plastics and bumper covers.
- Sets in 1 minute and sands after 15 minutes.
- Use with MixPac® Applicator Gun (PN08117).
- Use with 3M™ Automix™ Mixing Nozzle (PN08193).

Part Number	Cartridge Size	Cartridges Per Case
051131-04240	200ml	6

### 3M™ Automix™ Mixing Nozzle 3/8"

- Designed for use with MixPac® Applicator Gun (PN08117).



Part Number	Quantity Per Bag	Quantity Per Case
051131-08193	6	6

MixPac® is a registered trademark of MixPac® Systems AG, Switzerland.



### Duramix™ Super Fast Plastic Repair Adhesive

- A super fast-setting adhesive and repair material for rebuilding tab and fixing broken eyelets.
- Has excellent gap filling capabilities and withstands a wide range of temperatures, unlike cyanoacrylates.
- Use with MixPac® Applicator Gun (PN08117).
- Use with 3M™ Automix™ Mixing Nozzle (PN08193).

Part Number	Cartridge Size	Cartridges Per Case
051131-04247	200ml	6



### 3M™ Piranha™ Advanced Finishing Putty

- Two-component, self-leveling putty designed for use as a "skin" coat over plastic filler to fill pinholes, sand scratches, low areas and other imperfections.
- Cures tack-free in 30 minutes.
- Grips tight to galvanized steel, sanded paint, aluminum, steel, SMC, and fiberglass.
- Extremely easy sanding.
- Flowable and brushable.
- Non-staining.

Part Number	Container Size	Quantity Per Case
051131-05821	24 fl. oz.	6



### 3M™ Lightweight Body Filler

- Tack-free.
- Cures tack-free in 15–20 minutes — reduces sandpaper loading.
- Creamy texture.
- Smooth spreading.
- Easy sanding.
- Vacuum processed to minimize pinholes.

Part Number	Size/Net Wt.	Units Per Case
051131-05800	Quart (2 lbs./32 oz.)	6
051131-05801	Gallon (7.75 lbs./124 oz.)	4



## Welding/Bonding/Sealing

### 3M™ Flexiclear™ Body Seam Sealer

- High solids, clear joint and seam sealer designed to seal interior and exterior joints and seams.
- Adheres to primed metal and painted surfaces.
- Clear, non-yellowing.
- Excellent tooling properties.
- Can be painted quickly.
- Remains flexible.



Part Number	Container Size	Cartridges Per Case
051135- <b>08405</b>	Fits 1/10 Gallon Cartridge Gun	12

### 3M™ Super Silicone Sealant

- Rapid-curing adhesive/sealant formulated to solve repair and maintenance problems.
- Excellent gasket adhesive and form-in-place gasket material.
- Adheres to a wide variety of automotive surfaces.



Part Number	Color	Container Size	Cartridges Per Case
<b>Cartridges</b>			
051135- <b>08663</b>	Clear	Fits 1/10 Gallon Cartridge Gun	12
051135- <b>08664</b>	Black	Fits 1/10 Gallon Cartridge Gun	12

### 3M™ Spreaders

- Designed for spreading body and fiberglass fillers, finishing putties, and resins.
- Sharp edge.
- Flexible.
- Durable.
- Easy to clean.
- Cured filler pops off easily.



Part Number	Size	Units Per Case
051131- <b>05844</b>	Assortment: 1 each — 4", 5", and 6"	24

### 3M™ Creme Hardener

- Red creme hardening agent designed to be used with 3M™ Lightweight Body Filler (PNs 05800 and 05801).
- Creamy consistency mixes easily and quickly with any of the above products.



Part Number	Size/Net Wt.	Units Per Case
051131- <b>05830</b>	2.75 oz. Tube	12

### 3M™ General Purpose Adhesive Cleaner

- Specially blended solvent.
- Provides easy cleanup of most types of adhesives.
- Quickly removes waxes, road tars, grease, oil and similar materials.
- Will not harm most thoroughly cured automotive paint, vinyl or fabrics when properly used.
- Rated at 738 grams per liter of volatile organic compounds (VOC).
- Local air quality regulations may regulate or prohibit the use of surface preparation and cleanup materials based on VOC content. Consult your local air quality regulations.



Part Number	Container Size	Containers Per Case
051135- <b>08984</b>	1 Quart Can	6
051135- <b>08987</b>	15 oz. Aerosol Can	12

### 3M™ Woodgrain and Stripe Remover

- For removal of adhesive residue.
- Jelly-like consistency keeps remover in place on vertical surfaces to promote fast action when sprayed from the aerosol can.
- Follow up with the use of 3M™ Woodgrain and Stripe Adhesive Remover (PN08908).



Part Number	Container Size	Cans Per Case
051135- <b>08907</b>	24 oz. Aerosol Can	6

### 3M™ Woodgrain and Stripe Adhesive Remover

- Cleans off adhesive residue after woodgrain vinyl or vinyl stripes have been removed.
- Fast-acting remover can be used on all acrylic enamel painted metal surfaces.
- Jelly-like consistency keeps remover in place on vertical surfaces to promote fast-action when sprayed from an aerosol can.
- Saves on repair and repaint of the metal surface.



Part Number	Container Size	Cans Per Case
051135- <b>08908</b>	24 oz. Aerosol Can	6

# Safety

## 3M™ Bodyman Respirator Packout P100

- Facepiece respirators may be used up to 10X OSHA PEL or applicable government standard, whatever is lower. If exposure levels are not known, use a 3M Fresh Air system.
- NIOSH 42 CFR 84 approved.
- Reusable design — changeable filters.
- **3M recommended for grinding, sanding, welding and asbestos.**
- Activated carbon layer removes nuisance level organic vapors and odors.
- At least 99.97% filtration efficiency against solid and liquid aerosols including oils.



## 3M™ Automotive Professional Series Half Facepiece Paintspray Packout

- Designed for those respirator users who desire a re-usable respirator, the Professional Series from 3M is the latest innovation in comfort and durability for the automotive technician.
- Lightweight with a swept-back cartridge design for good vision and excellent balance.
- Unique head harness design adds stability and comfort.
- 3M™ Cool Flow™ Valve helps reduce heat and moisture build-up.
- Thin-wall design around the nose adds comfort.
- Fully maintainable — made of a liquid silicone material, it is designed for use with replacement cartridges, filters and spare parts as needed.
- **3M recommended for paint spray applications.**
- Facepiece is also adaptable to the 3M Dual Airline Supplied Air “Fresh Air” systems.
- NIOSH 42 CFR 84 approved.

Part Number	Size/Description	Packouts Per Case
051131-07181	<b>Small</b> – 3M™ Facepiece (07024), 4 (2-pack) of P100 filters (07184)	20
051131-07182	<b>Medium</b> – 3M™ Facepiece (07025), 4 (2-pack) of P100 filters (07184)	20
051131-07183	<b>Large</b> – 3M™ Facepiece (07026), 4 (2-pack) of P100 filters (07184)	20

## 3M™ Disposable Organic Vapor Half Facepiece Respirator Assembly P95

- Half Facepiece respirators may be used up to 10X OSHA PEL or applicable government standard, whichever is lower.
- NIOSH 42 CFR 84 approved.
- Maintenance-free design.
- Permanently attached cartridges with replaceable filters.
- **3M recommended for paint spray applications.**
- At least 95% filtration efficiency against solid and liquid aerosols including oils.



Part Number	Size/Description	Packouts Per Case
051131-37077	<b>Small</b> 3M™ Automotive Professional Series Half Facepiece Respirator (37081), 1 pair organic vapor cartridges (07046), 1 pair retainers (07054), 2 pairs of P95 filters (07194)	4
051131-37078	<b>Medium</b> 3M™ Automotive Professional Series Half Facepiece Respirator (37082), 1 pair organic vapor cartridges (07046), 1 pair retainers (07054), 2 pairs of P95 filters (07194)	4
051131-37079	<b>Large</b> 3M™ Automotive Professional Series Half Facepiece Respirator (37083), 1 pair organic vapor cartridges (07046), 1 pair retainers (07054), 2 pairs of P95 filters (07194)	4

Part Number	Size/Description	Assemblies Per Case
051131-07191	<b>Small</b> – 3M™ Organic Vapor Respirator (07191), 2 filter retainers (07054), 2 P95 filters (07194)	12
051131-07192	<b>Medium</b> – 3M™ Organic Vapor Respirator (07192), 2 filter retainers (07054), 2 P95 filters (07194)	12
051131-07193	<b>Large</b> – 3M™ Organic Vapor Respirator (07193), 2 filter retainers (07054), 2 P95 filters (07194)	12

3M products shown in this catalog must be used in accordance with OSHA regulations, and the User Instructions, warnings and limitations accompanying each product.

**WARNING: RESPIRATORS**

These respirators help reduce exposure to certain airborne contaminants. Misuse may result in sickness or death. Before use, the wearer must read and understand User Instructions provided as a part of product packaging. Time use limitations may apply. Call 3M OH&ESD Technical Service. 1 800 243-4630.

**IMPORTANT:** Before using these respirators, you must determine the following: 1) The type of contaminant(s) for which the respirator is being selected; 2) The concentration level of contaminant(s); 3) Whether the respirator can be properly fitted on the wear's face. All respirator instructions, warnings and use and time limitations must also be read and understood by the wearer before use.

Before use of these respirators, a written respiratory protection program must be implemented, meeting all the requirements of OSHA 29 CFR 1910.134, including training and fit testing.

Monitoring of exposure levels in applications such as paint spray must be done to determine cartridge change-out schedules.

# Safety

## 3M™ Full Facepiece Respirator Organic Vapor/P95 Packout

- Full Facepiece respirators may be used up to 50X OSHA PEL or applicable government standard, whichever is lower, when quantitatively fit tested.
- Facepiece is adaptable to the 3M Dual Airline Supplied Air "Fresh Air" Systems.
- **3M recommended for paint spray applications.**
- Fully maintainable — reusable design with replaceable filters and cartridges.
- Affords limited eye protection.
- Face shield covers available to protect face shield.
- At least 95% filtration efficiency against solid and liquid aerosols including oils.
- NIOSH 42 CFR 84 approved.



Part Number	Size/Description	Packouts Per Case
051131-07161	<b>Small</b> 3M™ Full Facepiece Respirator Organic Vapor/P95 Packout (07161), 1 pair organic vapor cartridges (07046), 1 pair retainers (07054), 2 pairs of P95 filters (07194), 2 face shield covers (07142)	2
051131-07162	<b>Medium</b> 3M™ Full Facepiece Respirator Organic Vapor/P95 Packout (07162), 1 pair organic vapor cartridges (07046), 1 pair retainers (07054), 2 pairs of P95 filters (07194), 2 face shield covers (07142)	2
051131-07163	<b>Large</b> 3M™ Full Facepiece Respirator Organic Vapor/P95 Packout (07163), 1 pair organic vapor cartridges (07046), 1 pair retainers (07054), 2 pairs of P95 filters (07194), 2 face shield covers (07142)	2

## 3M™ Organic Vapor Cartridge/95 Filter Replacement Packout

- Used to replace the cartridges and filters on the following respirators: 07024, 07025, 07026, 07138, 07139, 07140, 07161, 07162, 07163, 07177, 07178, 07179, 37077, 37078 and 37079.



Part Number	Quantity Per Case
051131-07195	5

## 3M™ Organic Vapor Monitor with Analysis

- Use to determine exposure levels of certain organic vapors in mixing and paint operations.
- Pre-paid analysis allows the user to send the exposed monitor to a 3M Laboratory for analysis (instructions included in package).
- Exposure levels are calculated and a report is sent which will assist the user in determining respirator selection and cartridge service life.



Part Number	Quantity Per Case
051131-37023	1

## 3M™ Particulate Respirator N95

- New braided straps for increased comfort.
- NIOSH 42 CFR 84 approved.
- **3M recommended for grinding and sanding.**
- Lightweight completely disposable dust respirator.
- Easy to talk through.
- At least 95% filtration efficiency against solid and liquid aerosols that do not contain oil.



Part Number	Respirators Per Box	Boxes Per Case
051131-07048	20	8

## 3M™ Particulate Respirator R95

- NIOSH 42 CFR 84 approved.
- **3M recommended for undercoating and rustproofing.**
- Can also be used for grinding, sanding and buffing.
- 3M recommended for nuisance level organic vapor relief.\*\*
- At least 95% filtration efficiency against solid and liquid aerosols that do not contain oil.



Part Number	Respirators Per Box	Boxes Per Case
051131-07187	20	6

\*\*Nuisance level organic vapor relief refers to reducing the irritating effects of concentrations not exceeding OSHA PEL or applicable government standard, whichever is lower.

3M products shown in this catalog must be used in accordance with OSHA regulations, and the User Instructions, warnings and limitations accompanying each product.

**WARNING: RESPIRATORS**

These respirators help reduce exposure to certain airborne contaminants. **Misuse may result in sickness or death.** Before use, the wearer must read and understand User Instructions provided as a part of product packaging. Time use limitations may apply. Call 3M OH&ESD Technical Service. 1 800 243-4630.

**IMPORTANT:** Before using these respirators, you must determine the following: 1) The type of contaminant(s) for which the respirator is being selected; 2) The concentration level of contaminant(s); 3) Whether the respirator can be properly fitted on the wear's face. All respirator instructions, warnings and use and time limitations must also be read and understood by the wearer before use.

Before use of these respirators, a written respiratory protection program must be implemented, meeting all the requirements of OSHA 29 CFR 1910.134, including training and fit testing.

Monitoring of exposure levels in applications such as paint spray must be done to determine cartridge change-out schedules.


# Safety

## 3M™ GVP PAPER Kit

- Kit includes all of the components that make up our PAPR with Bumpcap system with one easy-to-order part number. It includes the following which make a complete PAPR (Powered Air Purifying Respirator) system:
  - 1 Bumpcap with Wide View Face Shield 37008
  - 1 Breathing Tube 37012
  - 1 Comfort Belt-Mounted PAPR Assembly
    - Motor Blower GVP-100 (PN29206)
    - Battery GVP-111 (PN29208)
    - Charger GVP-112 (PN29209)
    - Flow Meter GVP-113 (PN29210)
    - Power Cord GVP-110 (PN29207)
    - Blower Plugs GVP-115 (PN29212)
    - Flow Meter Adapter L-181 (PN72792)
    - Comfort Belt 37054
  - 1 Organic Vapor/HEPA Cartridge GVP-441 (PN07196)
  - 1 Shower Cover GVP-119 (PN54304)
  - 5 Peel-Off Lens Covers
    - Replacement 37014, 25 Pack
    - Replacement 37015, 100 Pack
- 3M™ GVP PAPR Kit 07190 combines a high level of protection for automotive technicians with exceptional performance and versatility.
- Added features/benefits of the 07190 kit include:
  - No additional hoses to carry
  - Mobility
  - Wide-view lens headgear options with liftable lens
  - Excellent airflow
  - Multiple filter/cartridge options
  - One size fits most technicians
- 8-hour battery life.
- Applications include painting, sanding and grinding.
- NIOSH approved.



Part Number	Quantity Per Case
051131-07190	1



**WARNING: RESPIRATORS**

These respirators help reduce the exposure to certain airborne contaminants. **Misuse may result in sickness or death.** For proper use, see package, supervisor or call 3M OH&ESD Technical Service at 1-800-243-4630. In Canada, call 1-800-267-4414.

3M positive pressure respirators are to be used only by qualified persons properly trained in their use and maintenance, an only in accordance with their operating and maintenance manuals. Each person using these products must first read and understand the User Instructions. These products do not provide primary eye and face impact protection.

Monitoring of exposure levels in applications such as paint spray must be done to determine cartridge change-out schedules.


## 3M™ Respirator Training Programs

A very important component of many safety programs is respiratory protection. But even the best product will not provide the desired level of protection if it does not fit properly or is not worn during all times of exposure. 3M provides comprehensive training programs and materials to assist in respirator selection, respirator fitting and regulation compliance. More information is available on page 22.



3M products shown in this catalog must be used in accordance with OSHA regulations, and the User Instructions, warnings and limitations accompanying each product.

# Safety



## 3M™ Foam Ear Plugs

- Use to help protect hearing from loud and constant noises generated by grinding, sanding, buffing, or engine work.
- Provides comfortable and effective noise reduction (Noise Reduction Rating (NRR) is 28dB\*) with the convenience of disposability.
- Hypo-allergenic material.
- Available as individual ear plugs (PN37062) or with a soft, braided cord attached (PN37063) that provides accessibility and helps prevent loss.

Part Number	Description	Pairs per Box	Boxes Per Case
051131- <b>37062</b>	Ear Plug	200	5
051131- <b>37063</b>	Corded Ear Plug	100	5

\*NOTE: Research suggests that the NRR may overestimate the protection provided by hearing protectors during typical use. 3M recommends reducing the NRR by 50% for estimating the amount of noise reduction provided.

## ⚠ WARNING: HEARING PROTECTION PRODUCTS

These hearing protection products help prevent hearing loss against certain noises. To provide proper protection, the hearing protector should be (1) suitable for the job, (2) fitted properly in/on the ear, (3) worn during all times of exposure to noise, and (4) replaced when damaged or otherwise necessary. Failure to wear hearing protectors 100% of the time that your exposed to hazardous noise may dramatically increase your risk of developing hearing loss. Keep ear plugs away from infants and small children. They may get caught in a child's windpipe. For more information, call 3M OH&ESD Technical Service at 1-800-243-4630. In Canada, call 1-800-267-4414.

## 3M™ Safety Goggles

- Multi-purpose with polycarbonate lens.
- Flexible vinyl frames to enhance wearer comfort.
- Perforated for added ventilation.
- Do not use for protection against splash, fume or dust hazards.
- These high impact safety goggles are ANSI Z87.1-2003 compliant.



Part Number	Description	Goggles Per Box	Boxes Per Case
051131- <b>37102</b>	Clear, perforated	24	12

## ⚠ WARNING: HEAD AND FACE PROTECTION

These safety products provide limited protection only. **Misuse or failure to follow warnings and instructions may result in serious personal injury or death.** For proper use, see supervisor, product instructions and warnings or call 3M OH&ESD Technical Service at 1-800-243-4630. In Canada, call 1-800-267-4414.

## 3M™ Protective Eyewear

- Stylish contemporary design.
- Shatter resistant, polycarbonate lenses.
- Lightweight with gel-like nosepiece for exceptional comfort.
- Shaped to fit facial contours.
- Anti-scratch coating for longer use.
- 99% UV protection for outdoor use.
- Compliant with ANSI Z87.1-2003.
- Provides limited eye and face protection against flying particles.



Part Number	Description	Quantity Per Case
051131- <b>37113</b>	Grey frame, clear lens	24

## ⚠ WARNING: PROTECTIVE EYEWEAR

These safety products provide limited protection only. Do not use when performing torch burning, torch cutting, torch welding, electric (arc) welding, furnace corrections, molten metals operations, or any other operations which expose your eyes to harmful levels of infrared and ultra-violet radiation. **Misuse or failure to follow warnings and instructions may result in serious personal injury, including blindness or death.** For proper use, see supervisor, product instructions and warnings or call 3M OH&ESD Technical Service at 1-800-243-4630. In Canada, call 1-800-267-4414.

## 3M™ Health and Safety Services

3M e-Tools and on-site services can help you meet your safety goals and respiratory compliance requirements, as specified in OSHA Respiratory Protection Standard 29 CFR 1910.134.

### On-Line Respirator Medical Evaluations

This easy-to-use questionnaire helps establish the worker's clearance level for using a specific respirator in your work conditions. It can be completed in 15–30 minutes using any computer with internet access, and is available 24/7 to fit your employees' schedules. Any respirator brand can be used. You'll receive immediate notification of clearance as well as on-line record keeping to track employee status. Available in English and Spanish.

### On-Site Respirator Fit Testing Services

This service can help save valuable staff time and help reduce the cost of compliance. 3M Technicians will come to your site and can perform both qualitative and quantitative testing that is effective for all brands of respirator. This service includes fit testing provided by technicians trained in OSHA protocols and complete fit testing compliance documentation. Schedules can be set up to accommodate your multiple shifts and crews. Technicians will document results and provide summary reports.

**For more information on these services, please visit [www.respexam.com](http://www.respexam.com), call 1-800-383-3393 or contact your local 3M sales representative.**



3M products shown in this catalog must be used in accordance with OSHA regulations, and the User Instructions, warnings and limitations accompanying each product.

# Part Number Index

Part Number	Page	Part Number	Page	Part Number	Page	Part Number	Page
051131-01343	4	021200-06518	4	051131-16013	11	051131-16103	9
051131-01344	4	021200-06524	4	051131-16015	8	051131-16104	9
051131-01345	4	021200-06536	4	051131-16016	8	051131-16105	9
051131-01346	4	051131-06727	4	051131-16017	8	051131-16106	10
051131-01432	4	051131-06728	4	051131-16018	8	051131-16109	10
051131-01433	4	051131-06742	4	051131-16019	11	051131-16110	10
051131-01434	4	051131-06847	5	051131-16022	8	051131-16111	9
051144-01435	4	051131-06851	5	051131-16023	6	051131-16113	5
051144-01436	4	051131-06856	5	051131-16024	5	051131-16114	5
051144-01437	4	051131-06857	5	051131-16046	9	051131-16115	6
051144-01438	4	051131-07048	19	051131-16053	9	051131-16116	10
051144-01439	4	051131-07161	19	051131-16054	9	051131-16117	11
051144-01440	4	051131-07162	19	051131-16055	6	051131-16118	10
051144-01441	4	051131-07163	19	051131-16056	6	051131-16119	10
051144-01442	4	051131-07182	18	051131-16057	6	051131-16124	6
051144-01443	4	051131-07183	18	051131-16058	6	051131-16236	11
051131-01943	4	051131-07187	19	051131-16059	6	051131-16237	11
051131-01944	4	051131-07190	20	051131-16060	6	051131-16238	11
051131-01945	4	051131-07192	18	051131-16061	6	051131-16396	12
051131-04240	16	051131-07193	18	051131-16062	6	051131-16398	12
051131-04247	16	051131-07195	19	051131-16064	6	051131-16399	12
051131-05540	4	051131-07745	5	051131-16065	6	051131-16400	12
051131-05717	14	051131-07747	5	051131-16066	6	051131-26330	5
051131-05719	13	051131-07748	5	051131-16072	6	051131-26332	5
051131-05723	13	051131-08074	15	051131-16073	6	051131-26334	5
051131-05725	14	051135-08088	15	051131-16074	6	051131-26336	5
051131-05737	14	051135-08090	15	051131-16075	6	051131-26338	5
051131-05738	14	051135-08117	16	051131-16076	6	051131-26340	5
051131-05800	16	051131-08193	16	051131-16077	6	051131-26341	5
051131-05801	16	051135-08405	17	051131-16081	6	051131-37023	19
051131-05821	16	051135-08663	17	051131-16082	6	051131-37062	21
051131-05830	17	051135-08664	17	051131-16083	6	051131-37063	21
051131-05844	17	051135-08907	17	051131-16084	6	051131-37077	18
051131-05916	15	051135-08908	17	051131-16085	6	051131-37078	18
051131-05917	15	051135-08983	5	051131-16086	6	051131-37079	18
051131-05919	15	051135-08984	17	051131-16087	6	051131-37102	21
051131-05954	13	051135-08987	17	051131-16088	6	051131-37113	21
051131-05975	11	051131-16000	5	051131-16089	6	051131-37720	11
051131-06060	13	051131-16001	6	051131-16091	6	051131-38112	14
051131-06064	13	051131-16003	7	051131-16092	6	051131-38350	14
051131-06070	13	051131-16005	7	051131-16093	6	051131-39030	14
021200-06503	4	051131-16006	7	051131-16094	6		
021200-06506	4	051131-16007	8	051131-16095	6		
021200-06509	4	051131-16008	8	051131-16099	11		
021200-06512	4	051131-16010	11	051131-16102	9		

## Important Notice To Purchaser

**Product Use:** All statements, technical information and recommendations herein are based on tests 3M believes are reliable. 3M does not warrant or guarantee the accuracy or completeness of this information. User is responsible for determining whether this 3M product is fit for a particular purpose and suitable for user's method of application. Because there are many factors that can affect the use and performance of this product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate this product to determine whether it is fit for a particular purpose, is suitable for the user's method of application, and meets the user's performance specifications and expectations.

**Warranty and Limited Remedy:** 3M warrants that all products will upon delivery conform to 3M's published, written specifications. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective, your exclusive remedy shall be, at 3M's option, replacement or repair of the 3M product or refund of the purchase price of the 3M product.

**Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential.

## **Material Safety Data Sheets**

Fax On Demand (For five or less individual Material Safety Data Sheets)

**1-800-305-0419** (in the U.S. and Canada)

**651-732-6509** (outside North America)

For a complete set of Material Safety Data Sheets call:

**1-877-666-2277**

---

**For product information or additional questions call:**

**1-800-328-3908**

**Internet**

**[www.3Mgraphics.com](http://www.3Mgraphics.com)**



3M Center, Building 220-12E-04  
St. Paul, MN 55144-1000  
[www.3Mgraphics.com](http://www.3Mgraphics.com)

3M, Automix, Cool Flow, Duramix, Flexiclear,  
Hookit, Imperial, Paint Buster, Perfect-It, Piranha,  
PPS, Roloc, Scotch, SBS, Stikit and SUN GUN are  
trademarks of 3M.

Please recycle.  
Printed in U.S.A.  
© 3M 2007. All rights reserved.  
60-4401-0192-5