3M[™] Digital WallDisplay 9000 SERIES

Bring presentations to a whole new level.

- Dry erase screen
- Stereo sound system
- Space saving design
- Full connectivity
- Patented projection design
- 3M quality and reliability

000 SERIES

A GREAT IMAGE EVERYTIME!

3M Digital WallDisplay is an excellent alternative to projector installations, flat planel displays, and digital whiteboards. Integrating two commonly used meeting room tools of a digital projector and digital white board, 3M Digital WallDisplay allows you to communicate effectively and easily.

Get even more and take your presentations to a whole new level with the Digital WallDisplay 9000 series.

- Full digital whiteboard capabilities.
- · Remote collaboration for video conferencing.
- Draw, highlight, save, and distribute electronic presentations locally or around the world.
- Ultimate in presentation and communications!

The 3M Digital WallDisplay combines the functions of:

- · Multimedia projector
- Screen
- · Digital whiteboard
- TV monitor
- Write-on copyboard*
- Loudspeaker



OUUUDU

Projector
Speakers
Erasable Screen
Interactive Whiteboard
Remote Collaboration
Interactive Pens
Copyboard

•
•
•
1
•
•

OOODIW

020010







^{*} PCL 3 compatible printer required. Printer is not included.

3M™ Digital WallDisplay 9000 Series

COPYBOARD

Features:

- · Write/Draw notes on the large 60-inch surface
- Print the notes directly from the Digital WallDisplay to a connected printer.*

Minimum System Requirements:

- PCL-3 compatible printers. For a complete list of compatible printers please reference the 3M[™] Digital WallDisplay Operator's guide appendix. Forward compatible to PCL4 and PCL5 printers.
- · Printer not included.

INTERACTIVE WHITEBOARD

Features:

- Capture notes in color and save or send them in various file formats instantly (JPEG, GIF, TIFF, HTML, PDF, vector PDF, EPS, BMP 256 color, BMP monochrome, WBD) Powerpoint® (ppt & pps) and metafile (wmf)
- Interactive Display control computer mouse functions with the digital presentation pen
- Annotate and edit text and drawings on-line from remote locations
- Microsoft® NetMeeting® compatible
- Playback feature allows you to review all drawings on the board including erased items
- Import files from most business programs and annotate and save changes. (PPT, BMP, GIF, JPEG, ICO, EMF, WMF, Microsoft® Excel®, Clipboard files) Microsoft® Word® (doc & rtf)
- PC and Macintosh® compatible
- · On screen keyboard

Minimum System Requirements:

PC

- Microsoft® Windows® compatible computer with Pentium® 100+ Mhz processor
- Windows 98, 2000, ME, XP and Windows NT 4.0 compatible (other platform users may view shared meetings via Java™ applet through Java-enabled internet browser)
- 10 MB available hard drive space
- CD-ROM drive or Internet connection for software installation
- One available serial port or USB port (USV Serial Adapter required)



Visual Systems Division 3M Hong Kong Limited

5th Floor, Victoria Centre 15 Watson Road, Hong Kong Tel.: 2806 6111

Fax: 2807 1308 Website: www.3M.com/hk

9000 brings presentations to a whole new level.

Screen	Whiteboard with dry erase surface
Display Size	60" diagonal viewable area; 4:3 aspect ratio, 48"W x 36"H
Viewing Angle	170° horizontal, 170° vertical
Optical Structure	Single 0.7", DLP™ Texas Instruments technology,
	XGA (1024 x 768)
Colors	24 bit full color
ANSI Contrast Ratio	150:1 typical; 100:1 minimum
Lamp Type	VIP
Lamp Life	1600 Hours typical
Dimensions	47.6"H x 53.2"W x 7.0"D (1208mm x 1350mm x 179mm)
Wall-to-screen	7.05" (18cm) including mounting bracket
Weight	Approx. 85 lbs. (39 kg.)
Video Compatibility	NTSC, NTSC 4.43, PAL, PAL-N, PAL-M, SECAM
RGB Compatibility	VGA to SXGA: 640 x 480, 720 x 400, 800 x 600, 832 x 624,
	1024 x 768, 1152 x 864, 1280 x 1024
Mouse Emulation	Serial, ADB, USB
Computer Input	VGA, DVI-D
Video Input	Composite, S-video
Audio in	2 RCA jacks, 1 x 3.5mm stereo mini jack
Audio out	RCA jacks loop-through
Serial Control	9 pin D-Sub, RS-232
Audio amp	20 Watt per channel
Speakers	2 x 40w stereo 8 Ω
Power Requirements	Input 100-240 VAC, 50/60 Hz, 3 Wire Grounded, 355W. max
Environmental	
Operating	10-35°C, 10-85% RH, without condensation
Storage	-10-60°C, 10-85% RH, without condensation
Altitude	0-6000 feet above sea level
Regulatory	UL, CE, FCC Class A
Included Accessories	
Cables	Power Cord Set (US, UK, Euro), VGA Cable (2m), AV RCA cable (3m), S-video cable (2m), 3.5mm stereo mini cable (2m), RS232 Cable (2m)
Adapters	Macintosh™ to VGA Adaptor
Remote Control	IR Remote with navigator and mouse emulation, AAA batteries
Mounting Bracket	Single-position, fixed, hanging mount
User Interface	On-screen menu system; operable with or without remote
Presentation Tools	Reveal, Blank, Pointer, and Timer
Warranty	One year limited warranty on parts and labor

^{*} PCL 3 compatible printer required. Printer is not included.

Specifications subject to change without notice

Covered by U.S. Patents 6,179,426 and 442,205 Other patents are pending.

3M is a trademark of 3M Company. All other trade names referenced are the service marks, trademarks or registered trademarks of their respective companies.

Important Notice

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability

This product will be free from defects in material and manufacture for a period of 2 years from the date of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period, your exclusive memby shall be, at 3Ms option, to replace or repair the 4M product. Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.

Website: www.3M.com/hk/meetings E-mail: hkvsdsales@mmm.com