Product Description

Series 1160 is a high performance, durable, solvent-resistant transparent film with a non-stick nature. It is used to protect signs from most common types of tagging including flypost stickers. Designed to be applied as a protective overlay on any 3MTM Reflective or non-reflective sheeting, signs with this protection can be cleaned often with detergent and water to significantly restore performance and appearance saving time and the cost of replacement.



Application/Suitability

POF Series 1160 can be applied following 3M recommended guidelines to new, pre-cleaned signs manufactured with 3M Diamond GradeTM DG³, 3M High Intensity Prismatic (HIP), and 3M Engineer Grade Reflective Sheetings.

Effective Performance Life

POF Series 1160, when applied and maintained following 3M recommendations will have the same effective performance life as the base sheeting on which it is applied.

Note: Durability of the overlay may be reduced depending on cleaning frequency and solvents used.

Benefits

- Protects signface by allowing removal of dust, dirt and graffiti, so maintaining the life of signs
- Barrier to staining by many types of graffiti, including spray paint, permanent markers, lipstick, etc.
- Self adhesive stickers are easily removed
- Allows areas of a sign to be masked, then revealed months or years later
- Durable
- Saves replacement cost
- Provides additional protection to signfaces subject to frequent cleaning
- Resistant to most solvents

Product Construction / Specification

A durable, transparent film pre-coated with a pressure sensitive adhesive, protected by a plastic liner and provided with a pre-applied adhesive application tape. Suitable for use with 3M Diamond GradeTM DG³, 3M High Intensity Prismatic (HIP), Engineer Grade Reflective Sheetings and 3M ScotchcalTM Non Reflective Film.



Premium Protective Overlay Film

(POF) 1160

Cleaning

Signs protected with 1160 POF may be cleaned with a wide variety of cleaners though dilute, mild detergent and water or 3M Natural cleaner may be sufficiently effective whilst being easier and milder for those doing the cleaning.

Availability

For full product information please refer to the website or Customer Service Centre.

Application Surface

3M POF 1160 may be applied to new sign faces at the time of their manufacture. Application onto installed signs outdoors is not recommended

Product Information

For more detailed technical information please request the relevant product bulletin or download it from the website

For further information or samples, please contact: 3M Customer Service Centre on: 0161 237 6394 Or if within Republic of Ireland on: 01 280 3555

