


3M™ Overhead Projector 1700 Series



(Small)
meeting rooms

(Medium)
meeting rooms

technical data

Product Reference	1711	1720	1730	1780
Type of Projector	Transmissive	Transmissive	Transmissive	Transmissive
Lens Type	Open Singlet	Closed Singlet	Closed Doublet	Closed Doublet
Lens Focal Length	11.5"/293mm	11.5"/293mm	14"/355mm	14"/355mm
Lamp changer	No	No	No	Yes
Lamp Type & reference	82V-360W ENX	82V-360W ENX	82V-360W ENX	82V-360W ENX
Light Output (Lumens)	2500	2500	2500	2500
Fold down arm	No	No	No	No
Stage Aperture	10" x 10"	10" x 10"	10" x 10"	10" x 10"
Dimensions (W x D)	14.2" x 16.75"	14.2" x 16.75"	14.2" x 16.75"	14.2" x 16.75"
Weight	17.8 lb	17.8 lb	17.8 lb	19.2 lb
Voltage rating	120V/60 Hz	120V/60 Hz	120V/60 Hz	120V/60 Hz
Powercord Length	10 ft.	10 ft.	10 ft.	10 ft.
Agency Approval	UL/cUL	UL/cUL	UL/cUL	UL/cUL

3M™ Overhead Projector 1600 Series




(Small)
meeting rooms

technical data

Product Reference	1608	1610
Type of Projector	Transmissive	Transmissive
Lens Type	Open Singlet	Closed Singlet
Lens Focal Length	11.2"	11.5"
Lamp changer	Yes	No
Lamp Type	EHJ (24v/250w)	FCS (24v/150w)
Light Output (Lumens)	2000	1000
Fold down arm	Yes	No
Stage Aperture	11.25" x 11.25"	10" x 10"
Dimensions (W x D)	13.5" x 13.5"	12.5" x 13"
Weight	30 lb	11 lb
Voltage rating	120Vac,60 Hz	120Vac,60 Hz
Powercord Length	10 ft.	10 ft.
Agency Approval	UL/cUL	UL/cUL

3M™ Overhead Projector 2000 Series



technical data

(Small)
meeting rooms

(Small to Medium)
meeting rooms

Product Reference	2000	2660
Type of Projector	Reflective	Reflective
Lens Type	Open Singlet	Triplet varifocal
Lens Focal Length	11.5"	10.6 - 11.7"
Lamp changer with extra lamp	No	Yes
Lamp Type & reference	82V-250W EVW	24V-275W FNT
Light Output (Lumens)	1600	2500
Fold down arm	Yes	Yes
Stage Aperture	10.5 x 10.5"	11.25" x 11.25"
Dimensions (W x D)	13" x 19"	12.5" x 16.5"
Weight	14 lbs	11 lbs
Voltage rating	120Vac,60 Hz	120Vac,60 Hz
Powercord Length	10 ft.	10 ft.
Agency Approval	UL/cUL	UL/cUL